



Run time

55 min

[Normal mode]

Charging time

2.0_h

Max Sealed Suction

5.0 kPa

Max Air Flow

 $1.0 \, \text{m}^3/\text{min}$

12Vmax / 2.0Ah built-in type **Li-lon battery**

Improved dust-resistance



When capsule is installed securely, two ribs inside capsule press the inside frame of filter to hold the filter tight.











Dual-function indicator lamp





Indicates that the battery is being charged.

Charging time About





Warns of low battery capacity.

One-touch push button switch Single LED job light 3 Speed mode 2: High speed mode 3: Max speed mode 1: Normal speed mode Pipe locking blue mechanism 3 colors capsule section purple Pipe with beveled end Nozzle for flooring & carpet Hair removing brush Hair removing brush scrapes out and vacuums up

Accessories

Floor/carpet t-nozzle





Floor t-nozzle Part No. 123486-2



Part No. 459353-8



Flexible hose set Part No. 191E30-3





Flexible hose set Part No. 198868-7

Round brush set





Straight pipe set 340 Part No. 191D76-3





Sash nozzle holder Part No. 451242-3



Sash nozzle

hair/debris on carpet. Also available for wood floor.

Nozzle holder Part No. 459354-6





Long sash nozzle set

Part No. 198919-6





Filter H set Part No. 199989-8



Pre-filter Part No. 198750-0



Cyclone attachment set with pipe lock Part No.



Easy shake off filter B set Part No. 199966-0



Holder set Part No. 199971-7



Cordless Cleaner

CL117FD



≣O Built-in Job Light

Capacity Continuous Use (min.) Max air flow Max sealed suction Suction Power Dimensions (L x W x H)

Net weight

650 mL Powerful / High / Normal: 10 / 18 / 55 1.0 m³/min 5.0 kPa (510 mmH₂O) Powerful / High / Normal: 29 / 15 / 3

w/o Pipe & Nozzle: 457 x 110 x 136 mm (18 x 4-5/16 x 5-3/8") w/ Pipe & Nozzle: 992 x 110 x 136 mm (39 x 4-5/16 x 5-3/8") 1.0 kg (2.2 lbs.)

Standard Equipment: Floor nozzle, Sash nozzle, Sash nozzle holder, Pipe, Charger

Not covered by EPTA-Procedure Items of standard equipment and specifications may vary by country or area.



3-11-8 Sumiyoshi-cho, Anjo, Aichi, 446-8502 Japan